


CSB-508

8 zone emergency call signal central



Description


Compact 8-zone call signaling system compatible with the SB-504 emergency call signaling modules.

When activating the call from the SB-504 modules, the system emits an audible and visual warning both in the bathroom area and in the associated control panel. The call can be silenced by pressing the cancel button from the SB-504 bathroom module or from the CSB-508 central.

Incorporates an NO relay that stays closed as long as one or more calls are active.

Simple to install and easy to use. Can be mounted horizontally or vertically.

Dimensions




EQUIPOS Y SISTEMAS MEGAFONÍA / INTERCOM • PUBLIC ADDRESS SYSTEMS

UNIÓN DESARROLLOS ELECTRÓNICOS


Tel.: +34 934 772 854 / +34 609 914 787 • ude@udeaudio.com • BARCELONA - SPAIN

www.udeaudio.com

rev.2 | 610.535a | 1 / 3




- 1 [Led call indicator - Bathroom 1
Cancel call button. Bathroom 1
- 2 [Led call indicator - Bathroom 2
Cancel call button. Bathroom 2
- 3 [Led call indicator - Bathroom 3
Cancel call button. Bathroom 3
- 4 [Led call indicator - Bathroom 4
Cancel call button. Bathroom 4
- 5 [Led call indicator - Bathroom 5
Cancel call button. Bathroom 5
- 6 [Led call indicator - Bathroom 6
Cancel call button. Bathroom 6
- 7 [Led call indicator - Bathroom 7
Cancel call button. Bathroom 7
- 8 [Led call indicator - Bathroom 8
Cancel call button. Bathroom 8
- 9 [General call led indicators - Bathroom 1-8
General cancel-call button. Bathroom 1-8
- 10 [Visual light indicator - Active call.
- 11 [Light indicator ON.
- 12 [Acoustic warning - Active call.
- 13 [Wiring protection cover.



CENTRAL CSB-508

TERMINAL CONNECTION

- A POWER SUPPLY
2 cables of 1,50 mm² min. section
- B CORRIDOR DOME LIGHT CW-23
2 cables of 0,5 mm² min. section
- C CALL
1 cable of 0,25 mm² min. section



Connection diagram

